





Sondes de température

Type	MBT 3260	MBT 5250	MBT 5252	MBT 3560
				
Plage temp.	-50 - 120 °C	-50 - 200 °C	-50 - 200 °C	0 - 200 °C
Élément de résistance	1 x Pt 100	1 x Pt 100	1 x Pt 100	1 x Pt 1000
Longueur ins./déploiement	Ins. 50 - 250 mm	Ins. 50 - 200 mm	Déploiement 50 mm	Déploiement 33 mm
Racc. él.	DIN 43650, prise PG 9 (IP65)	DIN 43650/Pg 11	Type B / Pg 16	DIN 43650, plug Pg 9
Raccord	G 1/2 A	G 1/2 A	G 1/2 A	G 1/4 A