



Quick Selection

*Automatic Controls, Compressors
and Condensing units*

Table of contents

1. Expansion valves		7. Line components – Industrial	
Thermostatic expansion valves		Filters FIA, FIA-SS 104	Liquid level glasses LLG 106
Thermostatic expansion valves T2, TE2 6		8. Gas Detector	
Thermostatic expansion valves TE5-55 10		Gas detectors GD 108	
Thermostatic expansion valves TUA, TUAE and TCAE 14		9. Electronic controls	
Thermostatic expansion valves PHT 20		Refrigeration controllers EKC 315A 110 EKC 202 112
Electronically operated		Controller for appliance control AK-CC 550 114	Temperature controller EKC 102 116
Expansion valves AKV 24		Universal refrigeration controller AK-CC 210 118	System manager AK-SM 350 120
Electrical expansion valves ETS 28		Media temperature control EKC 361 122	Controller interface EKC 366 124
2. Solenoid valves and coils		Condenser fan speed controls XGE/RGE 126	Capacity controllers EKC 331T 128
Solenoid valves and coils EVR 30	 AK-PC 530 130	
Solenoid valves EVRA and EVRAT 32		10. Sensors and transmitters	
4-Way Reversing valves VHV and STF 34		Sensors and transmitters 132	
3. Pressure controls and thermostats		11. Compressors range	
Pressure controls and thermostats KP 36		Compressors 135	Direct current reciprocating compressors 137
Cartridge pressure controls ACB 38		Reciprocating Compressors 139	Scroll compressors 157
Thermostat UT 40		12. Condensing units range	
Pressure controls and thermostats RT 42		OPTYMA™ condensing units 171	
4. Pressure regulators			
Pressure regulators KVP 46			
Pressure regulators KVR and NRD 48			
Pressure regulators KVL 50			
Pressure regulators KVD 52			
Pressure regulators KVC 54			
Capacity regulator CPCE 56			
Motor valves ICM 20-65 58			
Pilot controlled servo valves ICS 25-65 62			
5. Water valves			
Pressure controlled water valve WVFX 68			
Thermostatic controlled water valves AVTA 70			
6. Line components – Commercial			
Ball valves GBC 72			
Check valves NRV and NRVH 74			
Oil separator OUB 76			
Heat exchanger HE 78			
Sight glasses SGN/H, SGR, SGRN/H 80			
Sight glasses SGI, SGR and SGRI 82			
Liquid line filter driers DCL 84			
Liquid line filter driers DML 86			
Filter driers DCR 88			
Bi-flow filter driers DMB 92			
Combi filter driers DMC 94			
Burn-out filter drier DAS 96			
Stop valves SVA 98			
Regulating valves REG and REG-SS 102			