

Technical Data

	KPI	KP
Media:	Liquid and gases	Gases*
Media temperature:	-40°C to 100°C	-40°C to 100°C
Ambient temperature:	-40°C to 65°C**	-40°C to 65°C**
Enclosure	IP30; with top cover or protection cap: IP44	IP30; with top cover or protection cap: IP44
Electrical connection:	Cable entry for diameters 6 mm to 14 mm	Cable entry for diameters 6 mm to 14 mm
Contact system:	SPDT	SPDT
Contact load:	AC-1 Ohmic 10A, 440V	16A, 400V
	AC-3 (motor) 6A, 440V	16A, 400V
	AC14/15 (coil/transformer) 4A, 440V	10A, 400V
	DC-13/14 12W, 220V	12W, 220V

*For liquids, please contact Danfoss

**Reduced life up to 80°C