







# Transmetteurs de pression

Type	MBS 33	MBS 3000	MBS 3050	MBS 4010	MBS 4510	MBS 5100	MBS 5150	MBS 4701	MBS 4751	EMP 2
										
<b>Plage de pression</b>	0 - 400 bar	0 - 400 bar	0 - 600 bar	0 - 16 bar	0 - 1 bar	0 - 100 bar	0 - 100 bar	0 - 100 bar	0 - 600 bar	-1 - 40 bar
<b>Sign. sortie</b>	4 - 20 mA	4 - 20 mA	4 - 20 mA	4 - 20 mA	4 - 20 mA	4 - 20 mA	4 - 20 mA	4 - 20 mA	4 - 20 mA	4 - 20 mA
<b>Tension</b>	10 - 30 V dc	10 - 30 V dc / 9 - 32 V dc	9 - 34 V dc	10 - 30 V dc	10 - 30 V dc	10 - 32 V dc	10 - 32 V dc	10 - 28 V dc	10 - 28 V dc	11 - 32 V dc
<b>Précision</b>	± 0,3% FS	± 0,5% FS	± 0,5% FS	± 0,3% FS	± 0,2% FS	± 0,1% FS	± 0,1% FS	± 0,3% FS	± 0,3% FS	± 0,5% FS
<b>Plage temp. fluide</b>	-40 - 85° C	-40 - 85° C	-40 - 85° C	-10 - 85° C	-10 - 85° C	-40 - 85° C	-40 - 85° C	-40 - 125° C	-40 - 125° C	-