



Krydshenvisning for OPTYMA PLUS R404A

Kølemiddel R404A	Hus		DANFOSS OPTYMA PLUS			TECUMSEH SILENSYS				Hus	
			Kode no.	Betegnelse	Køle kap. (W)	Betegnelse	Køle kap. (W)				
230 V/1 phase/50Hz -10/+32° C SH10K SC3K	H1	1	114X4100	MPHC010SCP00G	873	SIL-CAE 9450Z	843	1	H1		
			114X4108	MPHC018SCP00G	1.444	SIL-CAE 9460Z	972				
	114X4216		MPZC030MTP00G	2.238	SIL-CAJ 9480Z	1.391	H2				
					SIL-CAJ 9510Z	1.704					
					SIL-CAJ 9513Z	2.087					
					SIL-CAJ 4517Z	2.326					
					SIL-CAJ 4519Z	3.030					
			SIL-FH 4524Z	3.370							
230 V/1 phase/50Hz -35/+32° C RGT20 SC3K	H1	1	114X3108	LPHC018SCP00G	410	SIL-CAJ 2432Z	459	1	H1		
						SIL-CAJ 2440Z	531				
	114X3116		LPHC026GSP00G	724	SIL-CAJ 2446Z	711	H2				
					SIL-CAJ 2464Z	956					
	114X3224		LPHC048NTP00G	1.326	SI-FH 2480Z	1.263					
	114X3240		LPHC068NTP00G	2.041	SIL-FH 2511Z	1.679					
					SIL-TAJ 9480Z	1.391					
			SIL-TAJ 9510Z	1.704							
400 V/3 phase/50Hz -10/+32° C SH10K SC3K	H2	1	114X4224	MPZC030MTP00E	2.238	SIL-TAJ 9513Z	2.087	1	H1		
						SIL-TAJ 4517Z	2.326				
					SIL-TAJ 4519Z	3.030	H2				
					SIL-TFH 4524Z	3.370					
	114X4240		MPZC048MTP00E	4.266	SIL-TFH 4531Z	4.393					
	114X4256		MPZC060MTP00E	5.373	SIL-TFH 4540Z	5.173					
					SIL-TAG 4546Z	6.108	H3				
					SIL-TAG 4553Z	7.166					
	114X4364		MPZC086MTP00E	8.050	SIL-TAG 4561Z	7.617					
	114X4372		MPZC108MTP00E	9.689	SIL-TAG 4568Z	9.236					
					SIL-TAG 4573Z	9.791	H4				
					SIL-TAGD 4590Z	11.722					
					SIL-TAGD 4610Z	12.828					
			SIL-TAGD 4612Z	15.441							
			SIL-TAGD 4614Z	18.242							
400 V/3 phase/50Hz -35/+32° C RGT20 SC3K	H2	1	114X3232	LPHC048NTO00E	1.326	SIL-TAGD4615Z	19.353	1	H1		
						SIL-TAJ 2446Z	711				
	114X3248		LPHC068NTP00E	2.041	SIL-TAJ 2464Z	956	H2				
					SIL-THF 2480Z	1.263					
					SIL-TFH 2511Z	1.679					
	H3						SIL-TAG 2516Z		2.410	2	H3
							SIL-TAG 2522Z		2.986		
	H4						SIL-TAGD 2532Z		4.171	2	H4
							SIL-TAGD 2544Z		5.467		
			H4	2	114X3480	LPHC271NTP00E	9.232				

SH10K = SUPERHEAT 10° C (OVERHEDNING)
RGT20 = RETURN GAS TEMPERAURE 20° C (RETUR GAS TEMPERATUR)
SC3K = SUBCOOLING 3° C (UNDERAFKØLING)

Udover kølemiddel R404A, kan OPTYMA PLUS også anvendes med kølemidlerne R507, R134a og R407C

For nærmere information kontakt venligst dit Danfoss Salgsselskab - tlf 89 48 91 11

