



# VLT® AQUA Drive

## Phase conversion and speed control in a single, compact package

For applications such as lift stations, farming fields or any location where three-phase power is not available, UL-listed phase-converting VLT AQUA Drives can control three-phase motors using single-phase 240V or 480V service. Since three-phase motors are more readily available and less expensive, a variable frequency drive can be a cost-effective solution in these applications while providing an attractive alternative to conventional phase conversion devices. In addition, a drive provides numerous other benefits not available with traditional phase conversion units, including speed control, motor protection and energy savings.

Danfoss' unsurpassed experience in advanced variable frequency drive technologies makes the VLT AQUA Drive the perfect choice for all water and wastewater applications. The first drive designed specifically for water and wastewater applications, the VLT AQUA Drive offers the most advanced technology and features available in the market.



### Power range:

- 1-phase, 200–240 VAC: 1.5–30 HP
- 1-phase, 380–480 VAC: 10–50 HP

Feature	Benefit
<b>Dedicated features</b>	
• Modular design	• Facilitates maintenance and field upgrades
• Six-line LCP display	• Simultaneously displays multiple parameters
• Integrated Real-Time Clock	• Time stamping of functions/process control
• Enhanced Sleep Mode	• Improved energy savings/process control
• Initial Ramp	• Performance that matches pump demands
• Flow compensation	• Improved setpoint control
• De-ragging	• Removes strings and other debris from impeller
• End of pump curve detection	• Protects pump, detects leakage
• No/low flow detection	• Pump protection
• Pipe fill mode	• Eliminates water hammer
• Pulse counter with totalizer	• VFD can be programmed to shut down at a predefined number of gallons used
<b>Energy saving</b>	
• VLT efficiency of >98%	• Optimized performance
• Automatic Motor Adaptation (AMA)	• Optimal motor tuning without spinning motor shaft
• Automatic Energy Optimization	• Additional 5–15% energy savings
• Unique cooling concept	• Effective heat management
<b>Reliable</b>	
• Short circuit and ground fault protection	• Prevents damage to drive
• Line or motor phase imbalance monitoring	• Maintains full torque under extreme conditions
• Over and undervoltage protection	• Protects drive and motor
• Overtemperature monitoring	• Provides operation capabilities in extreme temperatures
• Electronic Thermal Protection	• Protects motor
• Optimum heat dissipation	• Lengthens drive life
• 100% factory load testing	• Ensures high reliability
• Optional conformal coating on PCBs available	• Provides additional protection in harsh environments



### Enclosure ratings

- **Available in Chassis, NEMA 1, NEMA 12 and NEMA 4X enclosures:** designed either for mounting in existing panels or as standalone units

### Available options

- **Modular application options:** plug-and-play cards facilitate drive upgrades, outdoor weather shield, and startup and servicing
- **dV/dt filters:** for providing motor isolation protection
- **Sine filters** (LC filters): reduce motor noise

### PC software tools

- **MCT 10:** provides powerful functionality for commissioning and servicing drives
- **VLT Energy Box:** comprehensive energy analysis tool
- **MCT 31:** harmonics calculation tool



Mains supply (L1, L2, L3)	
Supply voltage	1-phase 200–240 V ±10%; 1-phase 380–480 V ±10% (UL-listed)
Supply frequency	50/60 Hz
Displacement Power Factor (cos φ) near unity	(> 0.98)
Switching on input supply L1, L2, L3	1–2 times/min.
Output data (U, V, W)	
Output voltage	3-phase 200–240 V; 3-phase 380–480 V
Switching on output	Unlimited
Ramp times	1–3600 sec.
Closed loop	0–132 Hz
Digital inputs/outputs	
Programmable digital inputs (standard)	6 (two can be used as digital outputs)
General purpose I/O card (option)	3 additional digital inputs, 2 additional digital outputs
Logic	PNP or NPN
Voltage level	0–24 VDC
Analog inputs	
Analog inputs (standard)	2
General purpose I/O card (option)	2 additional analog inputs
Advanced analog I/O card (option)*	3 additional analog inputs
Modes	Voltage or current
Voltage level	-10 to +10 V (scaleable)
Current level	0/4 to 20 mA (scaleable)
Pulse inputs	
Programmable pulse inputs (standard)	2 (two of the digital inputs can be used as pulse inputs)
Voltage level	0–24V DC (PNP positive logic)
Pulse input accuracy	(0.1–110 kHz)
Analog outputs	
Programmable analog outputs (standard)	1
General purpose I/O card (option)	1 additional analog current output
Advanced analog I/O card (option)*	3 additional analog outputs
Current range at analog output	0/4-20 mA
Relay outputs	
Programmable relay outputs (standard)	2 (240 VAC, 2 A and 400 VAC, 2 A)
Relay card (option)	3 additional dry contact relays (240 VAC, Form C)
Voltage level	0–24V DC (PNP positive logic)
Pulse input accuracy	(0.1–110 kHz)
External DC supply	
External 24V DC supply card (option)	Provides backup power for control and option cards
Fieldbus communication	
FC Protocol and Modbus RTU built in (DeviceNet, Profibus and Ethernet IP modules optional)	
Ambient Temperature Rating	
0° C min – 50° C max	

\* Advanced analog I/O option card also provides backup power for the VLT® AQUA Drive's real-time clock.

[www.danfossdrives.com](http://www.danfossdrives.com)

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.

### Danfoss VLT Drives

4401 N. Bell School Road  
Loves Park, IL 61111, USA  
Phone: 1.800.432.6367  
1.815.639.8600  
FAX: 1.815.639.8000

### Danfoss VLT Drives

8800 W. Bradley Rd.  
Milwaukee, WI 53224, USA  
Phone: 1.800.621.8806  
1.414.355.8800  
Fax: 1.414.355.6117