



VLT® Low Harmonic Drives

VLT® AQUA Drive, VLT® AutomationDrive and VLT® HVAC Drive now available in low harmonic version

Where the performance of other low harmonic technologies depend on the stability of the grid and load or affect the controlled motor, the new Danfoss VLT® Low Harmonic Drives continuously regulate the network and load conditions without affecting the connected motor.

VLT® Low Harmonic Drives are motor friendly, with output impulse & shaft voltages compatible with motors conforming to IEC 60034-17/25 & NEMA-MG1-1998 part 31.4.4.2), as per standard VLT® Drives.

The VLT® Low Harmonic Drive has the same modular build-up as our standard high power drives and shares similar features: high energy efficiency, back-channel cooling and user-friendly operation.

The VLT® Low Harmonic Drive meets the toughest harmonic recommendations and gives the user full readout of the unit performance towards the grid, including graphical overview of grid behavior.



The perfect solution for

- > Meeting toughest harmonics recommendation/standards
- > Generator-powered installation
- > Installation with generator backup
- > Soft power grid
- > Installation of drives in grids with limited excess power capacity

Power Range

132 – 630 kW High Overload/
160 – 710 kW Normal Overload
(Matching drive frames D, E and F)

Enclosure degree

- > IP 21 / NEMA 1, IP 54 Hybrid

Voltage range

- > 380 – 480 V AC, 50 – 60 Hz

Features	Benefits
Energy saving	Lower operating costs
Energy saving functions (e.g., sleep mode, standby mode) Variable switching frequency for lower switching losses High product efficiency network changes	Saves energy
Reduced harmonics	Improved power factor/reduced load on supply network Lower transformer, switchgear and cable losses
Back-channel cooling (85% heat dissipated via back channel)	Less control room cooling Less fan power consumption
Unequalled robustness	Maximum up time
Robust enclosure	Maintenance free
Unique cooling concept with no ambient airflow over electronics	Problem-free operation in harsh environment
Coated PCBs	Problem-free operation in harsh environment
100% factory test	Problem-free operation
Highest possible harmonic mitigation	Save initial and operation cost
Maximum 5% THiD	Meeting toughest harmonics recommendation/standards
Robust against voltage imbalance and grid predistortion	Optimized transformer/generator grid capacity, more drives on same transformer
Dynamic regulation to load changes	Energy optimization
All built-in	low investment
Modular concept and a wide range of options	Low initial investment with maximum flexibility and possibility of future upgrades
Decentral I/O control via serial communication	Reduced cost for wiring and external I/O controller
Integrated EMC RFI filters	Meets EN55011 (A1 optional, A2 standard)
User friendly	Save commissioning and operation cost
Award-winning graphical display, 27 languages	Effective commissioning and operation
Full overview of grid condition	Reduced test effort
Timely tracking of grid conditions	Reduced test effort

PC software

MCT 10

Ideal for commissioning, servicing, monitoring and performance logging.

MCT 31

Harmonic calculation tool supporting VLT® Low Harmonic Drives.

RoHS compliant

VLT® Low Harmonic Drives are manufactured with respect for the environment and comply with the RoHS directive.

Options

> dV/dt filters:


Protect motor insulation

> Sine filters (LC filters):


Reduce motor noise

Back-channel cooling

A unique design uses a ducted back channel to pass cooling air over heat sinks with minimal air passing through the electronics area. This allows 85% of the heat losses to be exhausted directly outside of the enclosure, improving reliability and prolonging life by dramatically reducing temperature rise and contamination of the electronic components. There is an IP 54 seal between the back-channel cooling duct and the electronics area of the VLT® Low Harmonic Drive.



Specifications	
Harmonic mitigation performance	< 5% THD Meet individual harmonic levels of IEEE 519 for ISC/IL>20 Meeting EN/IEC61000-3-4/IEC61000-3-12
True power factor	> 0.98
Displacement factor	> 0.98
PC software & user interface	Commissioning tool function Configuration and installation settings function User settings and information function Control panel function Data logger and event log function Network monitoring and measurement function Filter load and status function Software update function
LCP Regulation	UL-file. CE marking, cULus (UL508C) and c-tick (AS/NZS 2064). IEEE519 / EN61000-3-xx harmonic mitigation guidelines IEEE587/ANSI C62.41/ EN61000-4-5 surge immunity EN55011 electromagnetic compatibility EN50178, EN60146 safety/design
Ambient temperature	-10° C to +45° C, up to 3280 feet above sea level, with relative humidity of 5% – 85% RH, class 3K3 (functions to be maintained up to 95% RH not condensing)
Power fuses	Optional
RFI filtering	Class A2 RFI; Class A1 RFI optional
Cooling	Air cooled with primary cooling through back channel



400 VAC (380-460 VAC)						
Normal Overload		High Overload		Frame	Dimensions	Weight
Power	Current	Power	Current		H x W x D	
kW	[A]	kW	[A]		IP 21 [mm]	kg
160	315	132	260	D	1740 x 1260 x 380	380
200	395	160	315			380
250	480	200	395			406
315	600	250	480	E	2000 x 1440 x 500	596
355	658	315	600			623
400	745	355	658			646
450	800	400	695			646
500	880	450	800	F	2200 x 3700 x 600	2009
560	990	500	880			2009
630	1120	560	990			2009
710	1260	630	1120			2009

Danfoss Drives, Division of Danfoss Inc., 4401 N. Bell School Rd., Loves Park, IL 61111, Tel. +1 (815) 639-8600 (main), Tel. +1 (800) 432-6367 (24h Service for Drives), Fax +1 (815) 639-8000, www.danfossdrives.com • E-mail: salesinformation@danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.